



Optanium T8 Instant Start

OPTANIUM ELE BALLAST (1) F32T8 347V

Reliable and energy efficient Philips Advance's Centium commercial grade specifications, plus added benefits of lamp striation reduction technology.

Product data

General Information	
Lamp Type	F32T8
Number of Lamps	1 piece/unit
Ballast Type	Electronic Fluorescent
Base Model	GOPA1P32LWSC
Suitable For Outdoor Use	Yes
Automatic Restart	Yes
Operating and Electrical	
Input Voltage	347 V
Input Frequency	50 to 60 Hz
Max THD	10 %
Starting Method	Instant Start
Lamp Current Crest Factor (Nom)	1.6
Ignition Time (Nom)	0.1 s
Ballast Factor (Nom)	0.78
Power Factor (Nom)	0.98
Input Current (Operating) (Nom)	0.07 A
Input Power (Nom)	24 W
Rated Lamp Watts	32 W

Wiring	
Color Input Terminals	No terminals
Color Output Terminals	No terminals
Wire Striplength	0.375 mm
Lamp Connection	Parallel
Wire Length by Color	See data sheet
Wire Gauge (Nom)	18AWG mm
Wire Type	Solid
Remote Wiring Configuration Allowed	Yes
Tandem Wiring Configuration Allowed	Yes
Through Wiring Configuration Allowed	Yes
Connector Type	No connector
Temperature	
T-Case Maximum (Nom)	70 °C
Mechanical and Housing	
Housing Material	Metal
Housing	N
Housing Dimensions	9.5" x 1.3" x 1.0"

Optanium T8 Instant Start

Approval and Application


EMC Immunity Standard	FCC Non-Consumer
Approbation Marks	CSA certificate UL certificate CEE Rated CSA E RoHS Compliant
Sound Rating	A
UL Recognized	No

Product Data

Order product name	OPTANIUM ELE BALLAST (1) F32T8 347V
--------------------	-------------------------------------

EAN/UPC - Product	781087142332
Order code	GOPA1P32LWN35M
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	30
Material Nr. (12NC)	913701265902
Net Weight (Piece)	350.000 g

Dimensional drawing



GOPA1P32LWN

Product	A1	A2	B1	C1
OPTANIUM ELE BALLAST (1) F32T8 347V	9.5 in	8.90 in	1.3 in	1.0 in

