

# BPL EM ballasts for CFL, PLT, PLS and PLC lamps (India)

## BPL 013 X261

Range of copper ballasts produced with a high level of accuracy on current settings to ensure optimum operation of compact fluorescent lamps. Designed for compact fluorescent lamps to be operated on 240 V-50 Hz mains supply.


### Product data

<b>Operating and Electrical</b>	
Input Voltage	240 V
Line Frequency	50 Hz
Input Frequency	50 Hz
<b>Wiring</b>	
Connector Type	Screw
<b>Approval and Application</b>	
Approval Marks	CE marking
<b>Product Data</b>	
Full product code	871150088432900

Order product name	BPL 013 X261
Order code	913702235112
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	20
Material Nr. (12NC)	913702235112
Full product name	BPL 013 X261
EAN/UPC - Case	8727900067217
EAN/UPC - Product/Case	8711500884329

BPL EM ballasts for CFL, PLT, PLS and PLC lamps (India)

Dimensional drawing



Product	D1	C1	A1	A2	B1
BPL 013 X261	4.2 mm	28.0 mm	87.0 mm	70.0 mm	39.0 mm

