



EB-E Electronic ballasts for TL-D lamps (India)

EBE 236 TLD 240

Compact, lightweight, high-frequency electronic ballast for TL-D lamps


Product data

| Operating and Electrical | |
|---------------------------------|---|
| Input Voltage | 220 to 240 V |
| Line Frequency | 50 to 60 Hz |
| Input Frequency | 50 to 60 Hz |
| Wiring | |
| Connector Type Input Terminals | WAGO 251 universal connector [Suitable for both automatic wiring (ALF and ADS) and manual wiring] |
| Connector Type Output Terminals | WAGO 251 universal connector [Suitable for both automatic wiring (ALF and ADS) and manual wiring] |
| Temperature | |
| Ambient temperature range | 0 °C to 50 °C |
| T-Case Maximum (Max) | 65 °C |
| Approval and Application | |
| Energy Efficiency Index | Not specified |

| Safety Standard | - [Not specified] |
|---------------------------------|-------------------|
| Product Data | |
| Order product name | EBE 236 TLD 240 |
| Full product name | EBE 236 TLD 240 |
| Full product code | 871150088486200 |
| Order code | 913702242112 |
| Material Nr. (12NC) | 913702242112 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8711500884862 |
| Numerator - Packs per outer box | 10 |
| EAN/UPC - Case | 8727900067880 |

EB-E Electronic ballasts for TL-D lamps (India)

Dimensional drawing



| Product | D1 | C1 | A1 | A2 | B1 |
|-----------------|--------|---------|----------|----------|---------|
| EBE 236 TLD 240 | 4.0 mm | 30.0 mm | 211.0 mm | 200.0 mm | 40.0 mm |

