



EB-T Electronic ballasts for TL-D lamps (India)

EBT 218 TLD

Compact, lightweight, high-frequency electronic standard ballasts for TL-D 36 W/ TL40 lamps


Product data

| Operating and Electrical | |
|---------------------------------|---|
| Input Voltage | 220 to 240 V |
| Line Frequency | 50 to 60 Hz |
| Input Frequency | 50 to 60 Hz |
| Wiring | |
| Connector Type Input Terminals | WAGO 251 universal connector [Suitable for both automatic wiring (ALF and ADS) and manual wiring] |
| Connector Type Output Terminals | WAGO 251 universal connector [Suitable for both automatic wiring (ALF and ADS) and manual wiring] |
| Temperature | |
| Ambient temperature range | 0 °C to 50 °C |
| T-Case Maximum (Max) | 75 °C |
| Approval and Application | |
| Energy Efficiency Index | A3 |

| Safety Standard | IEC 61347-2-3 |
|---------------------------------|-------------------|
| Approval Marks | CE marking S Mark |
| Product Data | |
| Order product name | EBT 218 TLD |
| Full product name | EBT 218 TLD |
| Full product code | 872790007852700 |
| Order code | 913702249112 |
| Material Nr. (12NC) | 913702249112 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8711500997029 |
| Numerator - Packs per outer box | 6 |
| EAN/UPC - Case | 8727900078527 |

EB-T Electronic ballasts for TL-D lamps (India)

Dimensional drawing



| Product | D1 | C1 | A1 | A2 | B1 |
|-------------|--------|---------|----------|----------|---------|
| EBT 218 TLD | 4.0 mm | 30.0 mm | 210.0 mm | 200.0 mm | 40.0 mm |

