

# HID-Basic Gearbox system for SON (India)

## BSN 250 X261

Impregnated electromagnetic ballasts of copper and steel construction for use in combination with an external ignitor for High-Pressure Sodium Vapor (SON) lamps

### Warnings and Safety

- Ballasts are only suitable for use with integrated luminaires


### Product data

Operating and Electrical	
Input Voltage	240 V
Line Frequency	50 Hz
Input Frequency	50 Hz
Wiring	
Connector Type	Screw
Approval and Application	
Energy Efficiency Index	Not specified
Approval Marks	CE marking

Product Data	
Order product name	BSN 250 X261
Full product name	BSN 250 X261
Full product code	871150088465700
Order code	913702253412
Material Nr. (12NC)	913702253412
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500884657
Numerator - Packs per outer box	4
EAN/UPC - Case	8727900067644

HID-Basic Gearbox system for SON (India)

Dimensional drawing



Product	D1	C1	A1	A2	B1
BSN 250 X261	6.3 mm	64.0 mm	150.0 mm	135.0 mm	75.0 mm

