



# Dynalite Leading Edge Dimmers

## DLE220

2 channel Leading Edge Dimmer Controller with a maximum load of 20 A per channel.



The Philips Dynalite DLE220 is a two-channel leading-edge dimmer controller, with a maximum load of 20 A per channel. Options available, including an additional RS-485 DyNet/DMX512 port, circuit-breaker trip reporting or neutral disconnect breakers

### Product data

General Information		Order product name	
CE mark	CE mark	DLE220	
Remarks	Please download the Lighting - Product Data Sheet for more information and ordering options	EAN/UPC – product	8710163505060
EU RoHS compliant	Yes	Order code	50506000
Application Conditions		SAP numerator – quantity per pack	1
Ambient temperature range	0 to +40 °C	SAP numerator – packs per outer box	1
		SAP material	913703002009
Product Data		Net Weight (Piece)	4.650 kg
Full product code	871016350506000		

# Dynalite Leading Edge Dimmers

## Dimensional drawing



Dynalite Leading Edge Dimmers

Dynalite Leading Edge Dimmers

