



# Dynalite Leading Edge Dimmers

## DLE220

2 channel Leading Edge Dimmer Controller with a maximum load of 20 A per channel.


The Philips Dynalite DLE220 is a two-channel leading-edge dimmer controller, with a maximum load of 20 A per channel. Options available, including an additional RS-485 DyNet/DMX512 port, circuit-breaker trip reporting or neutral disconnect breakers

### Product data


General Information		Order product name	DLE220
CE mark	CE mark	EAN/UPC – product	8710163505060
Remarks	Please download the Lighting - Product Data Sheet for more information and ordering options	Order code	50506000
RoHS mark	RoHS mark	Numerator – quantity per pack	1
		Numerator – packs per outer box	1
		Material no. (12NC)	913703002009
		Net weight (piece)	4.650 kg
Application Conditions			
Ambient temperature range	0 to +40 °C		
Product Data			
Full product code	871016350506000		

# Dynalite Leading Edge Dimmers

## Dimensional drawing



Dynalite Leading Edge Dimmers



Dynalite Leading Edge Dimmers

