



Dynalite Sensors

DUS30LHB-DALI

The Philips Dynalite sensor range combines motion detection, light level detection and IR receive in one unit. Each of these features can be operated at the same time, allowing automation scenarios such as turning on the lights after detecting motion and then dimming the lighting level once the available sunlight has been measured, thereby providing additional energy savings. By combining each of these functions into one device, operational efficiency is improved. Each sensor has an in-built microprocessor, allowing logical functions to control one small room, the floor of a building, or an entire building. All sensors receive their power from the DyNet network, and as they are fully remotely programmable, they can be configured to automate and control a virtually unlimited number of controlled outputs.

Product data

General Information		Full product name	DUS30LHB-DALI
Remarks	Please download the Lighting – Product Data Sheet for more information and ordering options	Full EOC	871869600512500
CE mark	CE mark	Order code	00512500
EU RoHS compliant	Yes	Material no. (12 NC)	913703015609
Temperature		Local order code	DUS30-LHB
Ambient temperature range	-5 to +50 °C	SAP numerator – quantity per pack	1
Product Data		EAN/UPC – Product/Case	8718696005125
Order product name	DUS30LHB-D	Numerator – packs per outer box	1
		EAN/UPC - Case	8718696012628