



# Dynalite Phase-Cut Dimmers

## DTE1210

Philips Dynalite supports a wide selection of dimmer units that are compatible with most lamp types. By selecting the right dimmer for the different lamp types, an unlimited number of combinations of dimmer units can be chosen to work together in one project. Utilizing the very latest in microprocessor technology, every Dynalite dimmer has many built-in dedicated features for the lighting control industry. Industry-leading 16-bit fading resolution allows ultra-smooth dimming in projects where this is critical for flicker-free scene changes. The dimmers are capable of fading from one scene to another over a period ranging from one second to 23 hours, triggered from a single network message. This allows simpler programming and a smooth transition from one scene to the next – a feature that is perfect for daylight harvesting in projects requiring energy management.

### Product data

General Information		Full product name	
Remarks	Please download the Lighting - Product Data Sheet for more information and ordering options	Full product code	871016350586200
CE mark	CE mark	Order code	50586200
EU RoHS compliant	Yes	Material Nr. (12NC)	913703022009
Temperature		Numerator - Quantity Per Pack	1
Ambient temperature range	0 to +40 °C	EAN/UPC - Product/Case	8710163505862
Product Data		Numerator - Packs per outer box	1
Order product name	DTE1210	EAN/UPC - Case	8710163505879

Dynalite Phase-Cut Dimmers

Dimensional drawing

