



# Dynalite Phase-Cut Dimmers

## DTE1210

Leading Edge Dimmer Controllers are ideal for lighting circuits with resistive and inductive properties, including mains voltage incandescent fittings, neon and low voltage lamps with a compatible electronic transformer. Available in both DIN-rail and wall box configuration, Dynalite supports a vast range of leading edge dimmer controllers with a variety of circuit numbers and sizes to work individually or part of a system, fitting any project requirement. Wall box dimmer controllers have been engineered to achieve rise times of over 100µS producing reduced filament sing, reduced supply voltage noise, resulting in extended lamp life. The dimmers are engineered to be compatible with electronic transformers, requiring less de-rating, therefore allowing full capacity of channel to be utilised.

### Product data

General Information		Full product name	
Remarks	Please download the Lighting - Product Data Sheet for more information and ordering options	Full product code	871016350586200
CE mark	CE mark	Order code	913703022009
EU RoHS compliant	Yes	Material Nr. (12NC)	913703022009
Temperature		Numerator - Quantity Per Pack	1
Ambient temperature range	0 to +40 °C	EAN/UPC - Product/Case	8710163505862
Product Data		Numerator - Packs per outer box	1
Order product name	DTE1210	EAN/UPC - Case	8710163505879

# Dynalite Phase-Cut Dimmers

## Dimensional drawing

