



# Dynalite Signal Dimmer Controllers

## DDBC1200

The Dynalite range of Signal Dimmer Controllers, have been engineered to meet the future demands of projects. They are capable of transmitting all industry standard driver protocols (1-10V, DSI, DALI and Broadcast DALI) and support two ranges of install opportunities of both DIN-rail and wall box, to allow for flexible install opportunities. The Signal Dimmer Controller range also support a vast range of driver controllers with a variety of circuit numbers and sizes to work individually or as part of a system, suiting any project requirement.

### Product data

<b>General Information</b>		<b>Full product code</b>	871869600687000
<b>Remarks</b>	Please download the Lighting - Product Data Sheet for more information and ordering options	<b>Local code description</b>	DDBC1200-V3
<b>CE mark</b>	CE mark	<b>Order code</b>	913703035109
<b>EU RoHS compliant</b>	Yes	<b>Material Nr. (12NC)</b>	913703035109
<b>Temperature</b>		<b>Local order code</b>	.
<b>Ambient temperature range</b>	+32 to +104 °F	<b>Numerator - Quantity Per Pack</b>	1
<b>Product Data</b>		<b>EAN/UPC - Product/Case</b>	8718696006870
<b>Order product name</b>	DDBC1200	<b>Numerator - Packs per outer box</b>	1
<b>Full product name</b>	DDBC1200	<b>EAN/UPC - Case</b>	8718696014370

# Dynalite Signal Dimmer Controllers

## Dimensional drawing

