



Dynalite Relay Controllers

DDRC810DT-GL

As one of the most popular forms of lighting control, relay and multi-use devices can have the greatest impact in terms of energy management and lighting control. Available in both DIN-rail and wall-box configurations, this Philips Dynalite solution enables a vast range of relay controllers with a variety of circuit numbers and sizes to work individually or as part of a system, thus fulfilling any project requirement. Each device can store over 170 presets, allowing the recall of complex switching logic from simple network messages. As the required preset scenarios are stored within each relay device, the commissioning process and network messages are simplified.

Product data

General Information			
Remarks	Please download the Lighting - Product Data Sheet for more information and ordering options	Full product name	DDRC810DT-GL
CE mark	CE mark	Full product code	871869600688700
EU RoHS compliant	Yes	Order code	00688700
		Material Nr. (12NC)	913703035209
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	8718696006887
		Numerator - Packs per outer box	1
		EAN/UPC - Case	8718696014387
Temperature			
Ambient temperature range	0 to +50 °C		
Product Data			
Order product name	DDRC810DT-GL		

Dynalite Relay Controllers

Dimensional drawing

