



Dynalite Relay Controllers

DMRC210

As one of the most popular forms of lighting control, relay and multi-use devices can have the greatest impact in terms of energy management and lighting control. Available in both DIN-rail and wall-box configurations, this Philips Dynalite solution enables a vast range of relay controllers with a variety of circuit numbers and sizes to work individually or as part of a system, thus fulfilling any project requirement. Each device can store over 170 presets, allowing the recall of complex switching logic from simple network messages. As the required preset scenarios are stored within each relay device, the commissioning process and network messages are simplified.

Product data

General Information		Full product name	DMRC210
Remarks	Please download the Lighting – Product Data Sheet for more information and ordering options	Full EOC	871016350688300
CE mark	CE mark	Order code	50688300
EU RoHS compliant	Yes	Material no. (12 NC)	913703050009
Temperature		SAP numerator – quantity per pack	1
Ambient temperature range	0 to +50 °C	EAN/UPC – Product/Case	8710163506883
Product Data		Numerator – packs per outer box	1
Order product name	DMRC210	EAN/UPC – Case	8710163506890

Dynalite Relay Controllers

Dimensional drawing

