



Dynalite Relay Controllers

DDRC810-GL

As one of the most popular forms of lighting control, relay and multi-use devices can have the greatest impact in terms of energy management and lighting control. Available in both DIN-rail and wall-box configurations, this Philips Dynalite solution enables a vast range of relay controllers with a variety of circuit numbers and sizes to work individually or as part of a system, thus fulfilling any project requirement. Each device can store over 170 presets, allowing the recall of complex switching logic from simple network messages. As the required preset scenarios are stored within each relay device, the commissioning process and network messages are simplified.

Product data

Product Data	
Order product name	DDRC810-GL
Full product name	DDRC810-GL
Full product code	871016350692000
Order code	913703051509
Material Nr. (12NC)	913703051509

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163506920
Numerator - Packs per outer box	1
EAN/UPC - Case	8710163506937