



Dynalite LED PWM Controllers

DDLEDC60035

Capable of directly driving LED fittings, the Dynalite LED Dimmers use Pulse Width Modulation (PWM) technology to great effect. Perfectly suited to Red, Green, Blue (RGB) color changing applications, chase sequencing or provision of elegant scene settings. The Dynalite LED drivers come in a range of configurations to meet the compatibility requirements of many of the available LED fittings. Each device is ready to receive native DMX allowing them to be used in color mixing or chase sequence applications.

Product data

General Information			
Remarks	Please download the Lighting - Product Data Sheet for more information and ordering options	Full product name	DDLEDC60035
CE mark	CE mark	Full product code	871016351704900
EU RoHS compliant	Yes	Order code	913703061309
		Material Nr. (12NC)	913703061309
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	8710163517049
		Numerator - Packs per outer box	1
		EAN/UPC - Case	8710163517056
Temperature			
Ambient temperature range	0 to +40 °C		
Product Data			
Order product name	DDLEDC60035		