



Dynalite Leading Edge Dimmers

DDLE801

8 channel Leading Edge Dimmer Controller at 1 A per channel


The Philips Dynalite DDLE801 supports eight channels of leading edge dimming at 1 A per channel. - It is suitable for use with incandescent lighting, as well as leading edge compatible magnetic and electronic transformers. - Advanced LED dimming technology makes the unit particularly suited to residential, retail and hospitality applications. - Active Load technology on each channelSoft start and voltage regulation technologiesSuperior internal drive componentry tuningFlexible mounting solution

Product data

General Information		Order product name	DDLE801
CE mark	CE mark	EAN/UPC – product	8718696001363
Remarks	Please download the Lighting - Product Data Sheet for more information and ordering options	Order code	00136300
RoHS mark	RoHS mark	Numerator – quantity per pack	1
		Numerator – packs per outer box	1
		Material no. (12NC)	913703061509
		Net weight (piece)	633.000 g
Application Conditions			
Ambient temperature range	-5 to +40 °C		
Product Data			
Full product code	871869600136300		

Dynalite Leading Edge Dimmers

Dimensional drawing



Dynalite Leading Edge Dimmers

