



# Dynalite Phase-Cut Dimmers

## DDLE801

Leading Edge Dimmer Controllers are ideal for lighting circuits with resistive and inductive properties, including mains voltage incandescent fittings, neon and low voltage lamps with a compatible electronic transformer. Available in both DIN-rail and wall box configuration, Dynalite supports a vast range of leading edge dimmer controllers with a variety of circuit numbers and sizes to work individually or part of a system, fitting any project requirement. Wall box dimmer controllers have been engineered to achieve rise times of over 100µs producing reduced filament sing, reduced supply voltage noise, resulting in extended lamp life. The dimmers are engineered to be compatible with electronic transformers, requiring less de-rating, therefore allowing full capacity of channel to be utilised.

### Product data

General Information			
Remarks	Please download the Lighting - Product Data Sheet for more information and ordering options	Full product name	DDLE801
CE mark	CE mark	Full product code	871869600136300
EU RoHS compliant	Yes	Order code	913703061509
		Material Nr. (12NC)	913703061509
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	8718696001363
		Numerator - Packs per outer box	1
		EAN/UPC - Case	8718696008867
Temperature			
Ambient temperature range	-5 to +40 °C		
Product Data			
Order product name	DDLE801		

## Dynalite Phase-Cut Dimmers

### Dimensional drawing

