



Dynalite Sensors

DUS30CS

The Philips Dynalite sensor range combines motion detection, light level detection and IR receive in one unit. Each of these features can be operated at the same time, allowing automation scenarios such as turning on the lights after detecting motion and then dimming the lighting level once the available sunlight has been measured, thereby providing additional energy savings. By combining each of these functions into one device, operational efficiency is improved. Each sensor has an in-built microprocessor, allowing logical functions to control one small room, the floor of a building, or an entire building. All sensors receive their power from the DyNet network, and as they are fully remotely programmable, they can be configured to automate and control a virtually unlimited number of controlled outputs.

Product data

General Information		Product Data	
Remarks	Please download the Lighting - Product Data Sheet for more information and ordering options	Order product name	DUS30CS
CE mark	CE mark	Full product name	DUS30CS
EU RoHS compliant	Yes	Full product code	871869688808700
Temperature		Order code	913703244309
Ambient temperature range	-20 to +45 °C	Material Nr. (12NC)	913703244309
Approval and Application		Numerator - Quantity Per Pack	1
Ingress protection code	IP20/54 [Finger-protected; dust accumulation-protected, splash-proof]	EAN/UPC - Product/Case	8718696888087
		Numerator - Packs per outer box	1
		EAN/UPC - Case	8718696895085

Dynalite Sensors

Dimensional drawing

