



Dynalite Multipurpose Controllers

DSM2

Within any project, many different lighting load types may be required to achieve a desired result. Each of these load types may require a different style of control. The Philips Dynalite range of multipurpose controllers allows customization of output types via different output module units. When using DIN-rail multipurpose controllers, a specific type of control can be chosen for each circuit: relay, leading-edge dimmer, trailing-edge dimmer, ballast control, controller with out-of-the-box functionality, fan control, and blind/screen control. In any combination, multiple load types can be controlled from a single device. This simplifies installation and prevents wasted capacity of circuits that are not required.

Product data

| General Information | |
|---------------------|---|
| Remarks | Please download the Lighting – Product Data Sheet for more information and ordering options |
| Product Data | |
| Order product name | DSM2 |
| Full product name | DSM2 |
| Full EOC | 871869600749500 |

| | |
|-----------------------------------|---------------|
| Order code | 00749500 |
| Material no. (12 NC) | 913703500509 |
| SAP numerator – quantity per pack | 1 |
| EAN/UPC – Product/Case | 8718696007495 |
| Numerator – packs per outer box | 1 |
| EAN/UPC – Case | 8718696014998 |

Dynalite Multipurpose Controllers

Dimensional drawing

