



Dynalite Sensors

DUS360CR-DALI

The Philips Dynalite sensor range combines motion detection, light level detection and IR receive in one unit. Each of these features can be operated at the same time, allowing automation scenarios such as turning on the lights after detecting motion and then dimming the lighting level once the available sunlight has been measured, thereby providing additional energy savings. By combining each of these functions into one device, operational efficiency is improved. Each sensor has an in-built microprocessor, allowing logical functions to control one small room, the floor of a building, or an entire building. All sensors receive their power from the DyNet network, and as they are fully remotely programmable, they can be configured to automate and control a virtually unlimited number of controlled outputs.

Product data

General Information		Full product name	DUS360CR-DALI
Remarks	Please download the Lighting - Product Data Sheet for more information and ordering options	Full product code	871869688710300
CE mark	CE mark	Order code	913703500909
EU RoHS compliant	Yes	Material Nr. (12NC)	913703500909
Temperature		Numerator - Quantity Per Pack	1
Ambient temperature range	0 to +45 °C	EAN/UPC - Product/Case	8718696887103
Product Data		Numerator - Packs per outer box	1
Order product name	DUS360CR-DALI	EAN/UPC - Case	8718696894101

Dynalite Sensors

Dimensional drawing

