



Dynalite Signal Dimmer Controllers

DMBC320-DALI-NA

The Dynalite range of Signal Dimmer Controllers, have been engineered to meet the future demands of projects. , They are capable of transmitting all industry standard driver protocols (1-10V, DSI, DALI and Broadcast DALI) and support two ranges of install opportunities of both DIN-rail and wall box, to allow for flexible install opportunities. , The Signal Dimmer Controller range also support a vast range of driver controllers with a variety of circuit numbers and sizes to work individually or as part of a system, suiting any project requirement.

The Dynalite range of Signal Dimmer Controllers, have been engineered to meet the future demands of projects. ;They are capable of transmitting all industry standard driver protocols (1-10V, DSI, DALI and Broadcast DALI) and support two ranges of install opportunities of both DIN-rail and wall box, to allow for flexible install opportunities. ;The Signal Dimmer Controller range also support a vast range of driver controllers with a variety of circuit numbers and sizes to work individually or as part of a system, suiting any project requirement.

Product data

General Information	
Remarks	Please download the Lighting - Product Data Sheet for more information and ordering options

Product Data	
Order product name	DMBC320-DALI-NA
Numerator – quantity per pack	1
Numerator – packs per outer box	1
Material no. (12NC)	913703531009

Dynalite Signal Dimmer Controllers

Net weight (piece)	0.001 kg
--------------------	----------

