



Dynalite Multipurpose Controllers

DMR316-UL

Within any project, many different lighting load types may be required to achieve a desired result. Each of these load types may require a different style of control. The Philips Dynalite range of multipurpose controllers allows customization of output types via different output module units. When using DIN-rail multipurpose controllers, a specific type of control can be chosen for each circuit: relay, leading-edge dimmer, trailing-edge dimmer, ballast control, controller with out-of-the-box functionality, fan control, and blind/screen control. In any combination, multiple load types can be controlled from a single device. This simplifies installation and prevents wasted capacity of circuits that are not required.

Product data

General Information		Full product code	871869600715000
Remarks	Please download the Lighting - Product Data Sheet for more information and ordering options	Local code description	DMR316-UL
CE mark	CE mark	Order code	913703667409
EU RoHS compliant	Yes	Material Nr. (12NC)	913703667409
		Local order code	.
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	8718696007150
		Numerator - Packs per outer box	1
		EAN/UPC - Case	8718696014653
Temperature			
Ambient temperature range	0 to +40 °C		
Product Data			
Order product name	DMR316-UL		
Full product name	DMR316-UL		

Dynalite Multipurpose Controllers

Dimensional drawing

