



Dynalite Multipurpose Controllers

DMR610GL-UL

Within any project, many different lighting load types may be required to achieve a desired result. Each of these load types may require a different style of control. The Dynalite range of multipurpose controllers allows customization of output types via different output module units. When using DIN-rail multipurpose controllers, a specific type of control can be chosen for each circuit: relay, leading-edge dimmer, trailing-edge dimmer, driver control, controller with out-of-the-box functionality, fan control, and blind/screen control. In any combination, multiple load types can be controlled from a single device. This simplifies installation and prevents wasted capacity of circuits that are not required.

Product data

| General Information | |
|---------------------|---|
| Remarks | Please download the Lighting - Product Data Sheet for more information and ordering options |
| CE mark | CE mark |
| EU RoHS compliant | Yes |

| Temperature | |
|---------------------------|-------------|
| Ambient temperature range | 0 to +40 °C |

| Product Data | |
|--------------------|-------------|
| Order product name | DMR610GL-UL |

| | |
|---------------------------------|-----------------|
| Full product name | DMR610GL-UL |
| Full product code | 871869688660100 |
| Order code | 913703668109 |
| Material Nr. (12NC) | 913703668109 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8718696886601 |
| Numerator - Packs per outer box | 1 |
| EAN/UPC - Case | 8718696893609 |

Dynalite Multipurpose Controllers

Dimensional drawing

