



# Dynalite Multipurpose Controllers

## DMD316FR-UL

Within any project, many different lighting load types may be required to achieve a desired result. Each of these load types may require a different style of control. The Philips Dynalite range of multipurpose controllers allows customization of output types via different output module units. When using DIN-rail multipurpose controllers, a specific type of control can be chosen for each circuit: relay, leading-edge dimmer, trailing-edge dimmer, ballast control, controller with out-of-the-box functionality, fan control, and blind/screen control. In any combination, multiple load types can be controlled from a single device. This simplifies installation and prevents wasted capacity of circuits that are not required.

### Product data

<b>General Information</b>		<b>Full product code</b>	871869688666300
<b>Remarks</b>	Please download the Lighting - Product Data Sheet for more information and ordering options	<b>Local code description</b>	DMD316-FR-UL
<b>CE mark</b>	CE mark	<b>Order code</b>	913703668709
<b>EU RoHS compliant</b>	Yes	<b>Material Nr. (12NC)</b>	913703668709
<b>Temperature</b>		<b>Local order code</b>	.
<b>Ambient temperature range</b>	0 to +40 °C	<b>Numerator - Quantity Per Pack</b>	1
<b>Product Data</b>		<b>EAN/UPC - Product/Case</b>	8718696886663
<b>Order product name</b>	DMD316FR-UL	<b>Numerator - Packs per outer box</b>	1
<b>Full product name</b>	DMD316FR-UL	<b>EAN/UPC - Case</b>	8718696893661

# Dynalite Multipurpose Controllers

## Dimensional drawing

