



Dynalite Multipurpose Controllers

DMD316FR-UL

Within any project, many different lighting load types may be required to achieve a desired result. Each of these load types may require a different style of control. The Philips Dynalite range of multipurpose controllers allows customization of output types via different output module units. When using DIN-rail multipurpose controllers, a specific type of control can be chosen for each circuit: relay, leading-edge dimmer, trailing-edge dimmer, ballast control, controller with out-of-the-box functionality, fan control, and blind/screen control. In any combination, multiple load types can be controlled from a single device. This simplifies installation and prevents wasted capacity of circuits that are not required.

Product data

General Information	
Remarks	Please download the Lighting - Product Data Sheet for more information and ordering options
CE mark	CE mark
EU RoHS compliant	Yes
Temperature	
Ambient temperature range	+32 to +104 °F
Product Data	
Order product name	DMD316FR-UL
Full product name	DMD316FR-UL

Full product code	871869688666300
Local code description	DMD316-FR-UL
Order code	913703668709
Material Nr. (12NC)	913703668709
Local order code	.
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696886663
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696893661

Dynalite Multipurpose Controllers

Dimensional drawing

