



Electronic ignitor for HID lamp circuits

SI 52

HID ignitors for parallel systems


Product data

General Information	
Application code	52
Operating and Electrical	
Input voltage	220 to 240 V
Input frequency	50 to 60 Hz
Ignition type	Parallel
Ignition voltage (max.)	0.75 kV
Ignition voltage (min.)	0.58 kV
Response voltage	190 V
Mains voltage performance (AC)	-8%+6%
Mains voltage safety (AC)	-10%+10%
Power losses (nom.)	0.5 W
Wiring	
Ballast contact wire cross section	0.50-2.50 mm ²
Connector type	Screw
Temperature	
T ambient (max.)	75 °C

T ambient (min.)	-20 °C
T-Case maximum (max.)	80 °C
Mechanical and Housing	
Housing	Akulon S223
Approval and Application	
Approval marks	CE marking
Product Data	
Full product code	871016303343300
Order product name	SI 52
EAN/UPC – product	8710163148595
Order code	913710010814
Numerator – quantity per pack	1
Numerator – packs per outer box	48
Material no. (12NC)	913710010814
Net weight (piece)	0.049 kg

Electronic ignitor for HID lamp circuits

Dimensional drawing



Product	C1	A1	A2	B1	D1
SI 52	38.5 mm	85.5 mm	65.0 mm	41.5 mm	4.3 mm

SI 52

