



# Electronic parallel ignitor for HID lamp circuits

## SI 52

HID ignitors for parallel systems


### Product data

| Operating and Electrical  |                 |
|---------------------------|-----------------|
| Input Voltage             | 220 to 240 V    |
| Line Frequency            | 50 to 60 Hz     |
| Input Frequency           | 50 to 60 Hz     |
| Wiring                    |                 |
| Connector Type            | Screw           |
| Temperature               |                 |
| Ambient temperature range | -20 °C to 75 °C |
| T-Case Maximum (Max)      | 80 °C           |
| Mechanical and Housing    |                 |
| Housing                   | Akulon S223     |

| Approval and Application        |                 |
|---------------------------------|-----------------|
| Approval Marks                  | CE marking      |
| Product Data                    |                 |
| Order product name              | SI 52           |
| Full product name               | SI 52           |
| Full product code               | 871016303343300 |
| Order code                      | 913710010814    |
| Material Nr. (12NC)             | 913710010814    |
| Numerator - Quantity Per Pack   | 1               |
| EAN/UPC - Product/Case          | 8710163148595   |
| Numerator - Packs per outer box | 48              |
| EAN/UPC - Case                  | 8710163033433   |

# Electronic parallel ignitor for HID lamp circuits

## Dimensional drawing



| Product | C1      | A1      | A2      | B1      | D1     |
|---------|---------|---------|---------|---------|--------|
| SI 52   | 38.5 mm | 85.5 mm | 65.0 mm | 41.5 mm | 4.3 mm |

