



# ET-S transformer

## ET-S 105 220-240V 50/60Hz

High-Frequency electronic transformer for operation with 12V halogen lamps, available in 70W, 105W and 150W versions


### Product data

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Inrush Current Width	0.16 ms
Wiring	
Connector Type Input Terminals	Screw
Connector Type Output Terminals	Screw
Cable Length From Device to Lamp	1.5 m
Temperature	
Ambient temperature range	-20 °C to 45 °C
T-Case Maximum (Max)	85 °C

Approval and Application	
Approval Marks	CE marking
Product Data	
Order product name	ET-S 105 220-240V 50/60Hz
Full product name	ET-S 105 220-240V 50/60Hz
Full product code	697013372903800
Order code	913710031661
Material Nr. (12NC)	913710031661
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6970133729038
Numerator - Packs per outer box	50
EAN/UPC - Case	6970133729045

ET-S transformer

Dimensional drawing



Product	D1	C1	A1	B1
ET-S 105 220-240V 50/60Hz	4.2 mm	33.5 mm	112.0 mm	54.0 mm

