



HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

BSN 150L 302I TS


The HID Basic Semi-Parallel ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.

Product data

Operating and Electrical		Full product name	
Input Voltage	230 V	BSN 150L 302I TS	
Line Frequency	50 Hz	Full product code	
Input Frequency	50 Hz	871016303103330	
		Order code	
		913710100750	
		Material Nr. (12NC)	
		913710100750	
		Numerator - Quantity Per Pack	
		1	
		EAN/UPC - Product/Case	
		8710163148182	
		Numerator - Packs per outer box	
		6	
		EAN/UPC - Case	
		8710163032023	
Wiring			
Connector Type	Screw		
Approval and Application			
Approval Marks	CE marking CCC certificate		
Product Data			
Order product name	BSN 150L 302I TS		

HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

Dimensional drawing



Product	D1	C1	A1	A2	B1
BSN 150L 302I TS	6.2 mm	64.5 mm	125.0 mm	110 mm	75.5 mm

