



# HID-Basic ballasts for HPL and HPI(PLUS) lamps

## BHL 400L 204


The HID-Basic ballast is an impregnated (HID standard) electromagnetic ballast for HID lamps, for use in combination with an external ignitor.

### Product data

General Information		Temperature	
Application Code	L204	T-Winding (Max)	130 °C
		Delta-T Normal Conditions	70 °C
Operating and Electrical		Approval and Application	
Input Voltage	240 V	Approval Marks	CE marking
Input Frequency	50 Hz	Product Data	
Power Factor 100% Load (Min)	0.85	Full product code	871016303212200
Mains Voltage Performance (AC)	-8% - +6%	Order product name	BHL 400L 204
Mains Voltage Safety (AC)	-10% - +10%	EAN/UPC - Product	8710163148267
Input Current with PF Correction	2.15 A	Order code	913710101350
Input Current without PF Correction	3.25 A	Numerator - Quantity Per Pack	1
Power Factor without PF Compensation (Nom)	0.60	Numerator - Packs per outer box	6
Power Losses (Nom)	23 W	Material Nr. (12NC)	913710101350
Wiring		Net Weight (Piece)	2.833 kg
Connector Type	Screw	System characteristics	
		Rated Ballast-Lamp Power	400 W

## HID-Basic ballasts for HPL and HPI(PLUS) lamps

### Dimensional drawing



Product	D1	C1	A1	A2	B1
BHL 400L 204	6.2 mm	64.5 mm	150.0 mm	135.0 mm	75.5 mm

BHL 400 L204

