

HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

BSN 150L 304I TS

The HID Basic Semi-Parallel ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.


Product data

General Information	
Application Code	L304 ITS
Operating and Electrical	
Input Voltage	240 V
Input Frequency	50 Hz
Power Factor 100% Load (Min)	0.85
Mains Voltage Performance (AC)	-8%~+6%
Mains Voltage Safety (AC)	-10%~+10%
Input Current with PF Correction	0.85 A
Input Current without PF Correction	1.8 A
Power Factor without PF Compensation (Nom)	0.40
Power Losses (Nom)	18.0 W
Wiring	
Connector Type	Screw
System characteristics	
Rated Ballast-Lamp Power	150 W

Temperature	
T-Winding (Max)	130 °C
Delta-T Normal Conditions	70 °C
Approval and Application	
Approval Marks	CE marking
Product Data	
Full product code	871016303115630
Order product name	BSN 150L 304I TS
EAN/UPC - Product	8710163148274
Order code	913710101550
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	913710101550
Net Weight (Piece)	1.900 kg

HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

Dimensional drawing



Product	D1	C1	A1	A2	B1
BSN 150L 304I TS	6.2 mm	64.5 mm	125.0 mm	110 mm	75.5 mm

BSN 150 L304 ITS

