



# HID-Basic ballasts for HPL and HPI(PLUS) lamps

## BHL 250L 201

The HID-Basic ballast is an impregnated (HID standard) electromagnetic ballast for HID lamps, for use in combination with an external ignitor.


### Product data

|                                 |              |
|---------------------------------|--------------|
| <b>Operating and Electrical</b> |              |
| Input Voltage                   | 220 V        |
| Line Frequency                  | 60 Hz        |
| Input Frequency                 | 60 Hz        |
| <b>Wiring</b>                   |              |
| Connector Type                  | Screw        |
| <b>Approval and Application</b> |              |
| Approval Marks                  | CE marking   |
| <b>Product Data</b>             |              |
| Order product name              | BHL 250L 201 |

|                                 |                 |
|---------------------------------|-----------------|
| Full product name               | BHL 250L 201    |
| Full product code               | 871016303468330 |
| Order code                      | 913710101850    |
| Material Nr. (12NC)             | 913710101850    |
| Numerator - Quantity Per Pack   | 1               |
| EAN/UPC - Product/Case          | 8710163034683   |
| Numerator - Packs per outer box | 6               |
| EAN/UPC - Case                  | 8710163034782   |

# HID-Basic ballasts for HPL and HPI(PLUS) lamps

## Dimensional drawing



| Product      | D1     | C1      | A1       | A2       | B1      |
|--------------|--------|---------|----------|----------|---------|
| BHL 250L 201 | 6.2 mm | 64.5 mm | 125.0 mm | 110.0 mm | 75.5 mm |

