



# HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

## BSN 150L 301I TS

The HID Basic Semi-Parallel ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.

### Product data

Operating and Electrical		Full product name		BSN 150L 301I TS	
Input Voltage	220 V	Full product code		871016303472030	
Line Frequency	60 Hz	Order code		913710102250	
Input Frequency	60 Hz	Material Nr. (12NC)		913710102250	
		Numerator - Quantity Per Pack		1	
		EAN/UPC - Product/Case		8710163148823	
		Numerator - Packs per outer box		6	
		EAN/UPC - Case		8710163034829	
Wiring					
Connector Type	Screw				
Approval and Application					
Approval Marks	CE marking				
Product Data					
Order product name	BSN 150L 301I TS				

HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

Dimensional drawing



Product	D1	C1	A1	A2	B1
BSN 150L 3011 TS	6.2 mm	64.5 mm	125.0 mm	110 mm	75.5 mm

