



# HID-Basic ballasts for HPL and HPI(PLUS) lamps

## BHL 400L 202

The HID-Basic ballast is an impregnated (HID standard) electromagnetic ballast for HID lamps, for use in combination with an external ignitor.

### Product data

Operating and Electrical	
Input Voltage	230 V
Line Frequency	50 Hz
Input Frequency	50 Hz
Wiring	
Connector Type	Screw
Approval and Application	
Approval Marks	CE marking
Product Data	
Order product name	BHL 400L 202

Full product name	BHL 400L 202
Full product code	871016303127930
Order code	913710102650
Material Nr. (12NC)	913710102650
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163148328
Numerator - Packs per outer box	6
EAN/UPC - Case	8710163032269

# HID-Basic ballasts for HPL and HPI(PLUS) lamps

## Dimensional drawing



Product	D1	C1	A1	A2	B1
BHL 400L 202	6.3 mm	64.5 mm	150.0 mm	134.0 mm	75.5 mm

