



HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

BSN 100L 302I

The HID Basic Semi-Parallel ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.

Product data

Operating and Electrical		Full product name		BSN 100L 302I
Input Voltage	230 V	Full product code		871016303141530
Line Frequency	50 Hz	Order code		913710103343
Input Frequency	50 Hz	Material Nr. (12NC)		913710103343
		Numerator - Quantity Per Pack		1
		EAN/UPC - Product/Case		8710163148441
		Numerator - Packs per outer box		6
		EAN/UPC - Case		8710163032405
Approval and Application				
Approval Marks	CE marking			
Product Data				
Order product name	BSN 100L 302I			

HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

Dimensional drawing

Product	D1	C1	A1	A2	B1
BSN 100L 302I	6.2 mm	51.5 mm	122.0 mm	107 mm	57.1 mm

