



HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

BSN 100L 300I

The HID Basic Semi-Parallel ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.

Product data

Operating and Electrical		Full product name		BSN 100L 300I	
Input Voltage	220 V	Full product code		871016303151430	
Line Frequency	50 Hz	Order code		913710103750	
Input Frequency	50 Hz	Material Nr. (12NC)		913710103750	
		Numerator - Quantity Per Pack		1	
		EAN/UPC - Product/Case		8710163031514	
		Numerator - Packs per outer box		6	
		EAN/UPC - Case		8710163032504	
Wiring					
Connector Type	Screw				
Approval and Application					
Approval Marks	CE marking				
Product Data					
Order product name	BSN 100L 300I				

HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

Dimensional drawing



Product	D1	C1	A1	A2	B1
BSN 100L 300I	6.2 mm	51.5 mm	122.0 mm	107 mm	57.1 mm

