

HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

BSN 70L 300I


The HID Basic Semi-Parallel ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.

Product data

| | | | | |
|--------------------------|--------------|---------------------------------|--|-----------------|
| Operating and Electrical | | Full product name | | BSN 70L 300I |
| Input Voltage | 220 V | Full product code | | 871016303260300 |
| Line Frequency | 50 Hz | Order code | | 913710104550 |
| Input Frequency | 50 Hz | Material Nr. (12NC) | | 913710104550 |
| | | Numerator - Quantity Per Pack | | 1 |
| | | EAN/UPC - Product/Case | | 8710163148502 |
| | | Numerator - Packs per outer box | | 6 |
| | | EAN/UPC - Case | | 8710163032603 |
| | | | | |
| Wiring | | | | |
| Connector Type | Screw | | | |
| | | | | |
| Approval and Application | | | | |
| Approval Marks | CE marking | | | |
| | | | | |
| Product Data | | | | |
| Order product name | BSN 70L 300I | | | |

HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

Dimensional drawing



| Product | D1 | C1 | A1 | A2 | B1 |
|--------------|--------|---------|----------|--------|---------|
| BSN 70L 300I | 6.2 mm | 51.5 mm | 117.0 mm | 102 mm | 57.1 mm |

