



HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

BSN 70L 301I


The HID Basic Semi-Parallel ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.

Product data

General Information		Temperature	
Application Code	L301I	T-Winding (Max)	130 °C
		Delta-T Normal Conditions	70 °C
Operating and Electrical		Approval and Application	
Input Voltage	220 V	Approval Marks	CE marking
Input Frequency	60 Hz		
Power Factor 100% Load (Min)	0.85	Product Data	
Mains Voltage Performance (AC)	-8%~+6%	Full product code	871016303162030
Mains Voltage Safety (AC)	-10%~+10%	Order product name	BSN 70L 301I
Input Current with PF Correction	0.45 A	EAN/UPC - Product	8710163148519
Input Current without PF Correction	0.98 A	Order code	913710104643
Power Factor without PF Compensation (Nom)	0.35	Numerator - Quantity Per Pack	1
Power Losses (Nom)	13 W	Numerator - Packs per outer box	6
Wiring		Material Nr. (12NC)	913710104643
Connector Type	Screw	Net Weight (Piece)	1.080 kg
System characteristics			
Rated Ballast-Lamp Power	70 W		

HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

Dimensional drawing



Product	D1	C1	A1	A2	B1
BSN 70L 301I	6.2 mm	51.5 mm	117.0 mm	102 mm	57.1 mm

BSN 70 L301 I

