

HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

BSN 600L 300I TS.


The HID Basic Semi-Parallel ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.

Product data

Operating and Electrical		Full product name	
Input Voltage	220 V	BSN 600L 300I TS.	
Line Frequency	50 Hz	Full product code	
Input Frequency	50 Hz	697480505081900	
		Order code	
		913710105942	
		Material Nr. (12NC)	
		913710105942	
		Numerator - Quantity Per Pack	
		1	
		EAN/UPC - Product/Case	
		6974805050819	
		Numerator - Packs per outer box	
		3	
		EAN/UPC - Case	
		6974805050826	
Wiring			
Connector Type	Screw		
Approval and Application			
Approval Marks	CE marking CCC certificate		
Product Data			
Order product name	BSN 600L 300I TS.		

HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

Dimensional drawing



Product	D1	C1	A1	A2	B1
BSN 600L 300I TS.	6.2 mm	82 mm	175 mm	160 mm	96.5 mm

