

HID-High Power ballasts for SON/MH lamps

BSN 1000L 3021


Impregnated (HID standard) electromagnetic ballasts, of copper/iron construction, for use in combination with an external ignitor, for HID lamps

Product data

Operating and Electrical		Full product name	
Input Voltage	230 V	Full product name	BSN 1000L 3021
Line Frequency	50 Hz	Full product code	871016305796530
Input Frequency	50 Hz	Order code	913710106750
		Material Nr. (12NC)	913710106750
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	8710163149189
		Numerator - Packs per outer box	1
		EAN/UPC - Case	8710163057972
Wiring			
Connector Type	Screw		
Approval and Application			
Approval Marks	CE marking CCC certificate		
Product Data			
Order product name	BSN 1000L 3021		

HID-High Power ballasts for SON/MH lamps

Dimensional drawing



Product	D1	C1	A1	A2	B1
BSN 1000L 302I	7 mm	102.0 mm	183 mm	134.5 mm	117.0 mm

