



HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

BSN 100L 300I TS

The HID Basic Semi-Parallel ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.

Product data

Operating and Electrical		Full product name	
Input Voltage	220 V	Full product code	697480505083300
Line Frequency	50 Hz	Order code	913710106842
Input Frequency	50 Hz	Material Nr. (12NC)	913710106842
Wiring		Numerator - Quantity Per Pack	1
Connector Type	Screw	EAN/UPC - Product/Case	6974805050833
Approval and Application		Numerator - Packs per outer box	6
Approval Marks	CE marking CCC certificate	EAN/UPC - Case	6974805050840
Product Data			
Order product name	BSN 100L 300I TS		

HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

Dimensional drawing



Product	D1	C1	A1	A2	B1
BSN 100L 300I TS	6.2 mm	51.5 mm	122.0 mm	107 mm	57.1 mm

