



HID-High Power ballasts for MH lamps

BMH 2000L 2050

The HID High-Power ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.

Product data

Operating and Electrical	
Input Voltage	400 V
Line Frequency	50 Hz
Input Frequency	50 Hz
Wiring	
Connector Type	Screw
Approval and Application	
Approval Marks	CCC certificate
Product Data	
Order product name	BMH 2000L 2050

Full product name	BMH 2000L 2050
Full product code	697480505087100
Order code	913710107242
Material Nr. (12NC)	913710107242
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6974805050871
Numerator - Packs per outer box	1
EAN/UPC - Case	6974805050888

HID-High Power ballasts for MH lamps

Dimensional drawing



Product	D1	C1	A1	A2	B1
BMH 2000L 2050	7 mm	102.0 mm	234 mm	185.5 mm	120.0 mm

