

HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

BSN 250L 300I TS


The HID Basic Semi-Parallel ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.

Product data

Operating and Electrical		Full product name	BSN 250L 300I TS
Input Voltage	220 V	Full product code	697480505079600
Line Frequency	50 Hz	Order code	913710109342
Input Frequency	50 Hz	Material Nr. (12NC)	913710109342
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	6974805050796
		Numerator - Packs per outer box	6
		EAN/UPC - Case	6974805050802
Wiring			
Connector Type	Screw		
Approval and Application			
Approval Marks	CE marking CCC certificate		
Product Data			
Order product name	BSN 250L 300I TS		

HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

Dimensional drawing



Product	D1	C1	A1	A2	B1
BSN 250L 300I TS	6.2 mm	64.5 mm	150.0 mm	135 mm	75.5 mm

