




HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

BSN 400L 300I TS

The HID Basic Semi-Parallel ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.


Product data

Operating and Electrical	
Input Voltage	220 V
Line Frequency	50 Hz
Input Frequency	50 Hz
Wiring	
Connector Type	Screw
Approval and Application	
Approval Marks	CCC certificate
Product Data	
Order product name	BSN 400L 300I TS

Full product name	BSN 400L 300I TS
Full product code	697480505011600
Order code	913710109542
Material Nr. (12NC)	913710109542
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6974805050116
Numerator - Packs per outer box	4
EAN/UPC - Case	6974805050123

HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

Dimensional drawing



Product	D1	C1	A1	A2	B1
BSN 400L 300I TS	6.2 mm	82 mm	165.0 mm	150 mm	96.5 mm

