



HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

BSN 400L 300I TS

The HID Basic Semi-Parallel ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.

Product data

Operating and Electrical		Full product name	
Input Voltage	220 V	Full product code	BSN 400L 300I TS
Line Frequency	50 Hz		697480505011600
Input Frequency	50 Hz	Order code	913710109542
		Material Nr. (12NC)	913710109542
		Numerator - Quantity Per Pack	1
Wiring		EAN/UPC - Product/Case	6974805050116
Connector Type	Screw	Numerator - Packs per outer box	4
		EAN/UPC - Case	6974805050123
Approval and Application			
Approval Marks	CCC certificate		
Product Data			
Order product name	BSN 400L 300I TS		

HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

Dimensional drawing



Product	D1	C1	A1	A2	B1
BSN 400L 300I TS	6.2 mm	82 mm	165.0 mm	150 mm	96.5 mm

