

# BTA EM ballasts for TL Fluorescent lamps

## BTA 18W 240V C DI

This efficient, reliable, long-life electromagnetic ballast for TL-D fluorescent lamps features a balanced combination of essential characteristics, thus allowing a wide variety of standard applications.


### Product data

Operating and Electrical	
Input Voltage	240 V
Line Frequency	50 Hz
Input Frequency	50 Hz
Wiring	
Connector Type	Double Insert
Mechanical and Housing	
Housing	L 155x39x28
Approval and Application	
Energy Efficiency Index	C
Approval Marks	CE marking

Product Data	
Full product code	871016303376130
Order product name	BTA 18W 240V C DI
Order code	913710112350
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	32
Material Nr. (12NC)	913710112350
Full product name	BTA 18W 240V C DI
EAN/UPC - Case	8710163033778
EAN/UPC - Product/Case	8710163148694

BTA EM ballasts for TL Fluorescent lamps

Dimensional drawing



Product	D1	C1	C3	A1	A2	A3	A4	B1	B2
BTA 18W	4.0	28.0	1.2	155.0	140.0	48.0	56.0	39.0	20.0
240V C DI	mm	mm	mm	mm	mm	mm	mm	mm	mm

