

# BTA EM ballasts for TL Fluorescent lamps

## BTA 18W 220V/60Hz C SC

This efficient, reliable, long-life electromagnetic ballast for TL-D fluorescent lamps features a balanced combination of essential characteristics, thus allowing a wide variety of standard applications.


### Product data

| Operating and Electrical |             |
|--------------------------|-------------|
| Input Voltage            | 220 V       |
| Line Frequency           | 60 Hz       |
| Input Frequency          | 60 Hz       |
| Wiring                   |             |
| Connector Type           | Screw       |
| Mechanical and Housing   |             |
| Housing                  | L 155x39x28 |
| Approval and Application |             |
| Energy Efficiency Index  | C           |
| Approval Marks           | CE marking  |

| Product Data                    |                        |
|---------------------------------|------------------------|
| Order product name              | BTA 18W 220V/60Hz C SC |
| Full product name               | BTA 18W 220V/60Hz C SC |
| Full product code               | 871016303543730        |
| Order code                      | 913710118343           |
| Material Nr. (12NC)             | 913710118343           |
| Numerator - Quantity Per Pack   | 1                      |
| EAN/UPC - Product/Case          | 8710163149943          |
| Numerator - Packs per outer box | 32                     |
| EAN/UPC - Case                  | 8710163065113          |

# BTA EM ballasts for TL Fluorescent lamps

## Dimensional drawing



| Product   | D1  | C1   | C3  | A1    | A2    | A3   | A4   | B1   | B2   |
|-----------|-----|------|-----|-------|-------|------|------|------|------|
| BTA 18W   | 4.0 | 28.0 | 1.2 | 155.0 | 140.0 | 48.0 | 48.0 | 39.0 | 20.0 |
| 220V/60Hz | mm  | mm   | mm  | mm    | mm    | mm   | mm   | mm   | mm   |
| C SC      |     |      |     |       |       |      |      |      |      |

