

BTA EM ballasts for TL Fluorescent lamps

BTA 36W 220V C 'SC

This efficient, reliable, long-life electromagnetic ballast for TL-D fluorescent lamps features a balanced combination of essential characteristics, thus allowing a wide variety of standard applications.

Product data


General Information		Temperature	
Application code	36W	T storage (max.)	80 °C
Design	C	T storage (min.)	-40 °C
Operating and Electrical		T-winding (max.)	130 °C
Input Voltage	220 V	Delta-T normal conditions	65 °C
Input frequency	50 Hz	Mechanical and Housing	
Mains voltage performance (AC)	-8%~+6%	Housing	L 155x39x28
Mains voltage safety (AC)	-10%~+10%	Approval and Application	
Power factor with PF compensation	0.85	Energy efficiency index	C
Power factor without PF compensation (nom.)	0.50	Approval marks	CE marking CCC certificate
Power losses (nom.)	8.8 W	Product Data	
Wiring		Full product code	871016306501430
Wire strip length	8.0 mm	Order product name	BTA 36W 220V C SC
Ballast contact wire cross section	0.50-1.00 mm ²	EAN/UPC – product	8710163149981
Connector type	Screw	Order code	06501430
System characteristics		SAP numerator – quantity per pack	1
Rated ballast-lamp power	36 W	Numerator – packs per outer box	32
		SAP material	913710119550

BTA EM ballasts for TL Fluorescent lamps

SAP net weight (piece)

0.460 kg

Dimensional drawing



BTA 36W 220V C 'SC

Product

BTA 36W 220V C SC

