

BTA EM ballasts for TL Fluorescent lamps

BTA 36W 220V C SC

This efficient, reliable, long-life electromagnetic ballast for TL-D fluorescent lamps features a balanced combination of essential characteristics, thus allowing a wide variety of standard applications.


Product data

| Operating and Electrical | |
|--------------------------|----------------------------|
| Input Voltage | 220 V |
| Line Frequency | 50 Hz |
| Input Frequency | 50 Hz |
| Wiring | |
| Connector Type | Screw |
| Mechanical and Housing | |
| Housing | L 155x39x28 |
| Approval and Application | |
| Energy Efficiency Index | C |
| Approval Marks | CE marking CCC certificate |
| | |

| Product Data | |
|---------------------------------|-------------------|
| Order product name | BTA 36W 220V C SC |
| Full product name | BTA 36W 220V C SC |
| Full product code | 871016306501430 |
| Order code | 913710119550 |
| Material Nr. (12NC) | 913710119550 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8710163149981 |
| Numerator - Packs per outer box | 32 |
| EAN/UPC - Case | 8710163065526 |

BTA EM ballasts for TL Fluorescent lamps

Dimensional drawing



| Product | D1 | C1 | C3 | A1 | A2 | A3 | A4 | B1 | B2 |
|-----------|-----|------|-----|-------|-------|------|------|------|------|
| BTA 36W | 4.0 | 28.0 | 1.2 | 155.0 | 140.0 | 48.0 | 50.0 | 39.0 | 20.0 |
| 220V C SC | mm | mm | mm | mm | mm | mm | mm | mm | mm |

