

BTA EM ballasts for TL Fluorescent lamps

BTA 18W 220V C 'SC

This efficient, reliable, long-life electromagnetic ballast for TL-D fluorescent lamps features a balanced combination of essential characteristics, thus allowing a wide variety of standard applications.


Product data

Operating and Electrical	
Input Voltage	220 V
Line Frequency	50 Hz
Input Frequency	50 Hz
Wiring	
Connector Type	Screw
Mechanical and Housing	
Housing	L 155x39x28
Approval and Application	
Energy Efficiency Index	C
Approval Marks	CE marking CCC certificate

Product Data	
Order product name	BTA 18W 220V C SC
Full product name	BTA 18W 220V C 'SC
Full product code	871016306502130
Order code	06502130
Material Nr. (12NC)	913710119750
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163150000
Numerator - Packs per outer box	32
EAN/UPC - Case	8710163065540

BTA EM ballasts for TL Fluorescent lamps

Dimensional drawing



Product	D1	C1	C3	A1	A2	A3	A4	B1	B2
BTA 18W	4.0	28.0	1.2	155.0	140.0	48.0	50.0	39.0	20.0
220V C SC	mm	mm	mm	mm	mm	mm	mm	mm	mm

